

Ideal for Routine Measuring



The MW 1150 is designed as a small compact laboratory instrument or atline instrument. It is based on the MW 11xx technology which allows readings within milliseconds to obtain sensor values quickly and reliably. The backlit 5.7" (14,5 cm) monitor displays the results - up to 250 readings can be stored in the system memory, atline applications use the standard 4-20mA interface to transfer values to a PLC. There are ports for a P 1150-type printer and various temperature sensors.

MW 1150 is set up and calibrated via a PC connection. The cables required and the software TEWS Moisture View Lite © are included in the package.

Almost all MW 4XXX-series laboratory sensors adapt to the MW 1150 circuitry.

MW 1150 introduces you to fast microwave moisture measuring at a reasonable cost.



Configuration The moisture analyzer comes as a compact instrument designed for IP20 protection and equipped with a backlit LCD graphics display and an integral sensor of any of the very many different types. Power is supplied through an external pluggable power supply.

Measuring range The actual measuring range is specific to the material under analysis and sensors, ranges from 0.1%-70.0% and can be selected in some sections. Supported product temperatures, ranging from 5°C to 60°C, are read using an optional external Pt100 or infrared temperature sensor and are compensated by optional using an automatic temperature-stabilized calibration.

Measuring time Less than one second

Product memory The EEPROM stores calibrations for up to 25 different products and a total of 250 measuring results.

Ports The instrument features an analog output (4-20mA), a USB port for PC connection, a port for external temperature sensor connection (Pt100 or IR), and a printer port for the optional TEWS thermotransfer printer P 1150.

Software Besides the on-board firmware, PC communication can be operated using the convenient software TEWS Moisture View Lite ©.

北京海菲尔格科技有限公司

地址：北京市朝阳区南磨房路37号华

腾北塘商务大厦1008室

邮编：100018

销售经理：孙远华

电话：13716489005

邮箱：13716489005@163.com

